

HUBBELL Power Systems

Compression Deadend

By FARGO
Catalog # [C100707NT](#)

Full tension double tongue compression deadend assembly for All Aluminum Conductors (AAC). Consists of a prefilled aluminum deadend body precompressed onto a steel adjustable clevis, two jumper terminals, and mounting hardware.



Features

- For use with AAC code names: Peony, Tulip, Daffodil
- Full tension Deadend assembly
- Steel Adjustable Clevis threaded stub factory compressed in deadend
- Prefilled with joint compound
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

| | |
|--|--|
| Bolt Installation Torque (Recommended) | 0 ft-lbs |
| Compression Method | Uni-Grip (single die system) |
| Die Size | 07CD |
| Material | Aluminum; Steel |
| Material - Body | Seamless Extruded Aluminum Alloy |
| Material - Clevis | Galvanized Forged Steel |
| Material - Hardware | Aluminum Alloy |
| Material - Pin (Cotter) | #304 Stainless Steel |
| Number of Bolt Holes | 2 |
| Number of Pad Holes | 0 |
| Press Minimum | 12 to |
| Product Category | Adjustable Clevis |
| Style | Uni-Grip, Double Tongue, Adjustable Clevis |
| Tension Range | 0 lb |
| Terminal Option | No |
| Type | Compression |

Dimensions

| | |
|------------------------------------|---------|
| Actual Clamp Strand Diameter Range | 0 in |
| Adjustment Step | 0 in |
| Angle - Pad | 0 ° |
| Bolt Diameter | 0.62 in |
| Clamping - Maximum | 0 in |
| Clamping - Minimum | 0 in |
| Diameter - Clamping Hardware | 0 in |
| Diameter - Clevis Pin | 0 in |
| Diameter - Eye Hole | 0 in |
| Diameter - Inside | 0 in |
| Diameter - Pad Bolt | 0 in |
| Length - Pin | 0 in |
| Length Before Compression | 16.4 in |
| Maximum Adjustment | 2.9 in |
| Messenger Diameter Range | 0 - 0 |
| Take Up | 0 in |
| Thickness - Pad | 0 in |
| Total Adjustment | 0 in |
| Width - Pad | 2 in |

Electrical Ratings

| | |
|---------------------|----------|
| Voltage Application | Standard |
|---------------------|----------|

Conductor Related

| | |
|--|---------------------|
| Clamping Range | 0- 0 |
| Conductor Compatibility | AAC-Daffodil-350-19 |
| Conductor Diameter (Main) - Maximum | 0 in |
| Conductor Diameter (Main) - Minimum | 0 in |
| Conductor Diameter (Main) Range | 0 - 0 |
| Conductor Diameter - Maximum | 0.68 in |
| Conductor Diameter - Minimum | 0.595 in |
| Conductor Diameter Range | 0.595 - 0.68 |
| Messenger Diameter - Maximum | 0 in |
| Messenger Diameter - Minimum | 0 in |

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-C100707NT-SPEC-EN | REV 6/2024