

Double Helical Cushion Suspension Assembly

By FARGO
Catalog # [DHCSA0690](#)

"The DHCSA is a bolted aluminum suspension clamp designed to provide enhanced conductor support and protection. The DHCSA combines a cast aluminum clamp assembly with helical aluminum alloy rod sets and EPDM rubber inserts. The rubber inserts are assembled directly onto the conductor and are held in place with helical rods. The clamp assembly is then bolted around the helical wrapped rubber supporting inserts to complete the install. Material: Clamp Body & Strap- Aluminum Alloy, Rubber Insert-EPDM Rubber, Helical Rods- Aluminum Alloy, Clamping Range: 0.871"-0.893", Helical Rod Color Code-Green, 12 Rods Per Set"

Features

- "The DHCSA clamps are rated for up to 250°C
- Designed for use on standard voltage applications with all aluminum, ACSR, ACSS, or aluminum alloy conductors
- The DHCSA clamps are two HCSA clamps with one shared set of helical rods
- Double Suspension for 30° - 60° line angle application
- Slip load is 15-20% of respective conductor RBS (Contact Hubbell for more Information)
- Application O.D. = (Helical Rod O.D. X 2) + Conductor O.D
- DHCSA is supplied with BNK and does not include fittings"

General

Type	Standard Voltage Suspension Clamps
UPC	096359727057



*Representative Image

Logistics

Pallet Quantity 28

Product Assets

[Literature - Suspension Clamps DHCSA \(SF05154E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Literature - Suspension Clamps DHCSA EHV \(SF05155E\)](#)
[Sales Drawings - CC-27022](#)

Related Products

[SA05 - Socket Eye](#)
[YCS059030 - Y-Clevis Eye, Rotated](#)
[CA05 - Clevis Eye Fitting](#)
[THCSA0690 - Trunnion Helical Cushion Suspension Assembly](#)