

HUBBELL Power Systems

Connector, Vise-Type

By FARGO

Catalog # [GA9843GAA](#)

Single Bolt Aluminum Vise-Type Connector



Oh No!
IMAGE COMING SOON

*Representative Image

Features

- Recommended for aluminum or aluminum to copper distribution, service or tap connections
- Sealant is recommended on all connectors
- Optional snap-on cover available

General

| | |
|--|----------------|
| Bolt Head Type | Hex |
| Bolt Installation Torque (Recommended) | 300 lb/ft |
| Catalog Number | GA9843GAA |
| EU RoHS Indicator | No |
| Grommets | Yes |
| Inhibitor Loaded | Yes |
| Material | Aluminum Alloy |
| Material - Body | Aluminum Alloy |
| Material - Bolt | Aluminum Alloy |
| Material - Hardware | Aluminum Alloy |
| Material - Keeper | Aluminum Alloy |
| Material - Spacer | Aluminum |
| Plating | No |
| Product Category | Clamps |
| Style | Single Bolt |
| UPC | 096359505464 |

Dimensions

| | |
|---------------------------|--------------------------------|
| Bolt Diameter | 0.5 |
| Diameter - Bolt | 0.5 in |
| Diameter - Bolt Head | 0.75 in |
| Dimensions | 2.000 in x 3.625 in x 3.750 in |
| Height | 3.75 in |
| Length | 2 in |
| Length - Nut Flat-To-Flat | 0.75 in |
| Weight | 0.86 lb |
| Width | 3.625 in |

Conductor Related

Conductor Compatibility

ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Brahma-203.2-16/19;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Tulip-336.1-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Snapdragon-900-61;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-

Certifications And Compliance

UL Listed

No

Logistics

Pallet Quantity

1600

Product Assets

[Catalogs - Distribution Connectors](#)

6/18;AAAC 6201 Alloy-Alliance-
246.9-6/18;ACAR-653.1-
12/7;ACAR-739.8-18/19

| | |
|--|-----------------|
| Conductor Diameter (Main) - Maximum | 1.031 in |
| Conductor Diameter (Main) - Minimum | 0.563 in |
| Conductor Diameter (Main) Range | 0.563 - 1.031 |
| Conductor Diameter (Tap) - Maximum | 0.563 in |
| Conductor Diameter (Tap) - Minimum | 0.316 in |
| Conductor Diameter - Maximum | 1.031 in |
| Conductor Diameter - Minimum | 0.563 in |
| Conductor Diameter Range | 0.563 - 1.031 |
| Conductor Type | Aluminum/Copper |



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-GA9843GAA-SPEC-EN | REV 6/2024