


# HUBBELL

## Power Systems

### Aluminum Automatic Dead End, 336.4 AAC,312.8 AAAC, 266.8 (18/1) ACSR Conductor, Clevis Bail.

By FARGO  
Catalog # [GD450](#)

Aluminum Automatic Dead End, 336.4 AAC,312.8 AAAC, 266.8 (18/1) ACSR Conductor, Diameter range .603 - .666" (15.32 - 16.92 mm), Clevis Bail.



\*Representative Image

#### Features

- Automatic Dead Ends for ACSR, AAC, and AAAC Conductor
- Galvanized steel stirrup clevis or Z-bail for primary applications and flexible or semi-flex bails for secondary applications
- Add "N" for neoprene covered Flex or Semi-flex bail
- Add "TA" for pulling eye (clevis bail only)

#### General

Bail Option	Clevis Bail
Catalog Number	GD450
Color Code	Brown
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Material - Bail	Galvanized Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Material - Shell	High Strength Aluminum Alloy
Product Category	Clevis Bail
Type	Automatic
UPC	096359309123

#### Dimensions

Assembly Rating (Ultimate)	10000 lb
Weight	2.65 lb

#### Conductor Related

Conductor Compatibility	ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7
Conductor Diameter - Maximum	0.666
Conductor Diameter - Minimum	0.603
Conductor Diameter Range	0.603 - 0.666

#### Product Assets

[Catalogs - Distribution Connectors](#)  
[Literature - Ropes Course Industry Letter \(April 2021\)](#)  
[Literature - Deadends For Overhead Connections](#)  
[Sales Drawings - GD-440A\\_Series\\_Overhead\\_Automatic\\_Deadend\(CC-25241\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
FG-GD450-SPEC-EN | REV 6/2024