

Copper Automatic Dead End, #4  
SOL Copper, 8A CW, Flex Bail.

By FARGO  
Catalog # [GD112](#)

Copper Automatic Dead End, #4 SOL Copper, 8A CW,  
Conductor Range .19 - .20" (4.9 -5.2 mm), Flex Bail.



\*Representative Image

Features

- Fastest method of deadending Copper and Copperweld® conductor
- Flared mouth of gripping unit permits easy conductor installation
- Four segment jaw is precision machined and automatically adjusts to the contour of the wire
- High strength alloy copper tube for gripping Copperweld® conductors

General

Bail Option	Flex Bail
Catalog Number	GD112
EU RoHS Indicator	Contact Manufacturer
Material	Copper; Steel
Material - Bail	Stainless Steel
Material - Shell	Copper Alloy
Product Category	Flex Bail
Type	Automatic
UPC	096359307914

Dimensions

Length	6.88 in
Weight	0.19 lb
Width	0.78 in

Conductor Related

Conductor Diameter - Maximum	0.2
Conductor Diameter - Minimum	0.19
Conductor Diameter Range	0.19 - 0.2

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	8400
-----------------	------

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - CC-24780](#)
- [Specifications - GD112](#)