

Copper Automatic Dead End, 2/0
SOL,1/0 STRCopper, 2A CW, Flex
Bail.

By FARGO
Catalog # [GD117](#)

Copper Automatic Dead End, 2/0 SOL,1/0 STR Copper, 2A CW,
Conductor Range .36 - .37" (9.1 - 9.3 mm) , Flex Bail.

Features

- Fastest method of deadending Copper and Copperweld® conductor
- Flared mouth of gripping unit permits easy conductor installation
- Four segment jaw is precision machined and automatically adjusts to the contour of the wire
- High strength alloy copper tube for gripping Copperweld® conductors

General

Bail Option	Flex Bail
Catalog Number	GD117
EU RoHS Indicator	Contact Manufacturer
Material	Copper; Steel
Material - Bail	Stainless Steel
Material - Shell	Copper Alloy
Product Category	Flex Bail
Type	Automatic



*Representative Image

UPC 096359308164

Dimensions

Weight 0.67 lb

Conductor Related

Conductor Diameter - Maximum	0.37
Conductor Diameter - Minimum	0.36
Conductor Diameter Range	0.36 - 0.37

Logistics

Pallet Quantity 3600

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - CC-24780](#)
- [Specifications - GD117](#)