


Aluminum Automatic Dead End, 4/0 AAC, 4/0 AAAC, 4/0 ACSR Conductor, Semi-Flex Bail.

By FARGO
Catalog # [GD469A](#)

Aluminum Automatic Dead End, 4/0 AAC, 4/0 AAAC, 4/0 ACSR Conductor, Diameter range .505 - .595" (12.83 -15.11 mm), Semi-Flex Bail.



*Representative Image

Features

- Automatic Dead Ends for ACSR, AAC, and AAAC Conductor
- Galvanized steel stirrup clevis or Z-bail for primary applications and flexible or semi-flex bails for secondary applications
- Add "N" for neoprene covered Flex or Semi-flex bail
- Add "TA" for pulling eye (clevis bail only)

General

Bail Option	Semi-Flex Bail
Color Code	Pink
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Material - Bail	Stainless Steel
Material - Shell	High Strength Aluminum Alloy
Product Category	Semi-Flex Bail
Type	Automatic
UPC	096359309253

Dimensions

Weight	0.980 lb
--------	----------

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;AAC-Oxlip-4/0-7
Conductor Diameter - Maximum	0.595
Conductor Diameter - Minimum	0.505
Conductor Diameter Range	0.505 - 0.595

Logistics

Pallet Quantity	800
-----------------	-----

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Literature - Deadends For Overhead Connections \(LEEDS-HPS-DEADEND-QUICK-REFERENCE-GUIDE-SF-EN-2023_Web\)](#)
[Sales Drawings - GD-440A_Series_Overhead_Automatic_Deadend\(CC-25241\)](#)
[Sales Drawings - CC-25241](#)

Related Products

[GD409A - Aluminum Automatic Dead End, 4/0 AAC, 4/0 AAAC, 4/0 ACSR Conductor, SS Flex Bail.](#)
[GD409AZ - Aluminum Automatic Dead End, 4/0 AAC, 4/0 AAAC, 4/0 ACSR Conductor, Z Bail.](#)
[GD449A - Aluminum Automatic Dead End, 4/0 AAC, 4/0 AAAC, 4/0 ACSR Conductor, Clevis Bail.](#)