

Copper Automatic Dead End, #4
SOL Copper, 8A CW Conductor,
Clevis Bail.

By FARGO
Catalog # [GD512](#)



Copper Automatic Dead End, #4 SOL Copper, 8A CW
Conductor, Diameter range .19 - .20" (4.9 -5.2 mm), Clevis Bail.

*Representative Image

Features

- Fastest method of deadending Copper and Copperweld® conductor
- Flared mouth of gripping unit permits easy conductor installation
- Four segment jaw is precision machined and automatically adjusts to the contour of the wire
- High strength alloy copper tube for gripping Copperweld® conductors

General

Bail Option	Clevis Bail
Catalog Number	GD512
EU RoHS Indicator	Contact Manufacturer
Material	Copper; Steel
Material - Bail	Galvanized Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Material - Shell	Copper Alloy
Product Category	Clevis Bail
Type	Automatic
UPC	096359309291

Dimensions

Length	6.88 in
Weight	0.59 lb
Width	0.78 in

Conductor Related

Conductor Diameter - Maximum	0.2
Conductor Diameter - Minimum	0.19
Conductor Diameter Range	0.19 - 0.2

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	3600
-----------------	------

Product Assets

[Catalogs - Distribution Connectors](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - CC-24780](#)
[Specifications - GD512](#)