

Aluminum Automatic Dead End,  
397.5 AAC, 394.5 AAAC, 336.4  
(18/1) ACSR Conductor, Semi-Flex  
Bail.

By FARGO  
Catalog # [GD471](#)

Aluminum Automatic Dead End, 397.5 AAC, 394.5 AAAC, 336.4  
(18/1) ACSR Conductor, Diameter range .659 - .724" (16.74 -  
18.39 mm), Semi-Flex Bail.

Features


- Automatic Dead Ends for ACSR, AAC, and AAAC Conductor
- Galvanized steel stirrup clevis or Z-bail for primary applications and flexible or semi-flex bails for secondary applications
- Add "N" for neoprene covered Flex or Semi-flex bail
- Add "TA" for pulling eye (clevis bail only)

General

Bail Option	Semi-Flex Bail
Catalog Number	GD471
Color Code	Green
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Material - Bail	Stainless Steel
Material - Shell	High Strength Aluminum Alloy
Product Category	Semi-Flex Bail
Type	Automatic
UPC	096359515869

Dimensions

Assembly Rating (Ultimate)	10000 lb
----------------------------	----------



\*Representative Image

Weight	1.67 lb
--------	---------

Conductor Related

Conductor Compatibility	ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Brahma-203.2-16/19;AAC-Daffodil-350-19
Conductor Diameter - Maximum	0.724
Conductor Diameter - Minimum	0.659
Conductor Diameter Range	0.659 - 0.724

Logistics

Pallet Quantity	320
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Deadends For Overhead Connections](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - CC-25241](#)
- [Specifications - GD471](#)