

HUBBELL Power Systems

Tie, Double Arm

By FARGO
Catalog # [GJ811FC](#)



Composite Double Pin Tie

*Representative Image

Features

Semi-Conductive tie provides uniform electrical field around attachment point.

General

Catalog Number	GJ811FC
Color Code	White
EU RoHS Indicator	No
Insulator Throat Neck Type	F Neck
Material	Composite
Material - Cover and Body	Semi-Conductive covering over Rigid Black PVC
Product Category	Ties
UPC	096359310891

Dimensions

Insulator Throat Diameter - Maximum	3.38 in
Insulator Throat Diameter - Minimum	2.75 in
Insulator Throat Diameter Range	2.75 - 3.38
Length	13.25 in
Weight	0.333 lb

Conductor Related

Conductor Diameter (Covered) - Maximum	0.406 in
Conductor Diameter (Covered) - Minimum	0.25 in
Conductor Diameter (Covered) Range	0.406-0.25
Conductor Diameter - Maximum	0.406
Conductor Diameter - Minimum	0.25
Conductor Diameter Range	0.25 - 0.406
Conductor Type	Covered

Logistics

Carton Quantity	100
Pallet Quantity	600

Product Assets

[Sales Drawings - CC-26432](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-GJ811FC-SPEC-EN | REV 6/2024