

HUBBELL Power Systems

Tie, Double Arm

By FARGO
Catalog # [GJ815FC](#)



Composite Double Pin Tie

*Representative Image

Features

Semi-Conductive tie provides uniform electrical field around attachment point.

General

| | |
|----------------------------|---|
| Catalog Number | GJ815FC |
| Color Code | Red |
| EU RoHS Indicator | No |
| Insulator Throat Neck Type | F Neck |
| Material | Composite |
| Material - Cover and Body | Semi-Conductive covering over Rigid Black PVC |
| Product Category | Ties |
| UPC | 096359310952 |

Dimensions

| | |
|-------------------------------------|-------------|
| Insulator Throat Diameter - Maximum | 3.38 in |
| Insulator Throat Diameter - Minimum | 2.75 in |
| Insulator Throat Diameter Range | 2.75 - 3.38 |
| Length | 13.25 in |
| Weight | 0.421 lb |

Conductor Related

| | |
|--|--------------|
| Conductor Diameter (Covered) - Maximum | 1.125 in |
| Conductor Diameter (Covered) - Minimum | 0.92 in |
| Conductor Diameter (Covered) Range | 1.125-0.92 |
| Conductor Diameter - Maximum | 1.125 |
| Conductor Diameter - Minimum | 0.92 |
| Conductor Diameter Range | 0.92 - 1.125 |
| Conductor Type | Covered |

Logistics

| | |
|-----------------|-----|
| Carton Quantity | 100 |
| Pallet Quantity | 600 |

Product Assets

[Sales Drawings - CC-26432](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-GJ815FC-SPEC-EN | REV 6/2024