

Copper Automatic Dead End, #3 SOL and #4 STR Copper, 6A CW Conductor, Clevis Bail.

By FARGO
Catalog # [GD513](#)

Copper Automatic Dead End, #3 SOL and #4 STR Copper, 6A CW Conductor, Diameter range .22 - .23" (5.7- 5.9 mm), Clevis Bail.

Features

- Fastest method of deadending Copper and Copperweld® conductor
- Flared mouth of gripping unit permits easy conductor installation
- Four segment jaw is precision machined and automatically adjusts to the contour of the wire
- High strength alloy copper tube for gripping Copperweld® conductors

General

Bail Option	Clevis Bail
Catalog Number	GD513
EU RoHS Indicator	Contact Manufacturer
Material	Copper; Steel
Material - Bail	Galvanized Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Material - Shell	Copper Alloy
Product Category	Clevis Bail
Type	Automatic
UPC	096359309307

Dimensions



*Representative Image

Length	6.88 in
Weight	0.55 lb
Width	0.78 in

Conductor Related

Conductor Diameter - Maximum	0.23
Conductor Diameter - Minimum	0.22
Conductor Diameter Range	0.22 - 0.23

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	3200
-----------------	------

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - CC-24780](#)
- [Specifications - GD513](#)