

## Automatic Splice, Bi-Metal (Copper to Aluminum)

By FARGO  
Catalog # [GL4042A11](#)

Automatic Splice, Bimetallic, #2 & #4 Stranded AAC, AAAC, ACSR to #6 Solid Copper



\*Representative Image

### Features

- Provide a mechanical and electrical connection of copper to ACSR, aluminum, or aluminum alloy conductors
- Individually bagged to seal out dirt before use.
- Factory loaded inhibitor to ensure long term corrosion free performance.

### General

Color Code	None
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy
UPC	096359311942

### Dimensions

Weight	0.392 lb
--------	----------

### Conductor Related

Conductor Compatibility	AAC-Rose-4-7;AAC-Iris-2-7;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18
-------------------------	--

### Certifications and Compliance

UL Listed	No
-----------	----

### Product Assets

- [Catalogs - Communication Connectors - Deadends and Splices](#)
- [Catalogs - Distribution Connectors \(CA05127E\)](#)
- [Literature - Quick Reference Guide: Splices for Overhead Connections \(LEEDS-HPS-SPLICES-QUICK-REFERENCE-GUIDE-SF-EN-2023\)](#)
- [Video - Hubbell Power Systems Automatic Splice Installation \(VI0548E\)](#)