

HUBBELL

Power Systems

Automatic Side Opening Wedge Deadend, #4 - 4/0 AAC, AAAC, ACSR, 3/0 str CU

By FARGO
Catalog # [GDW2040A](#)

Automatic Side Opening Wedge Deadend, AAC, AAAC, ACSR, Metric Conductor .230 - .570" (5.8 - 14.5 mm),



*Representative Image

Features

- Fastest method of deadending ACSR, AAAC, and AAC conductor
- Requires no wrenches or special tools
- Two-leg design
- Plated jaws available to accommodate copper conductors

General

Catalog Number	GDW2040A
Material	Aluminum Alloy
Material - Body	Aluminum Alloy
Material - Jaw	Aluminum Alloy
Material - Keeper	High Strength Aluminum Alloy
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Product Category	Wedge
Type	Automatic Side Opening Wedge
UPC	096359365327

Dimensions

Assembly Rating (Ultimate)	8000 lb
Dimensions	8.000 in x 4.900 in x 2.000 in
Height	2 in
Length	8 in
Weight	2 lb
Width	4.9 in

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Sparrow-2-6/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18
Conductor Diameter - Maximum	0.57
Conductor Diameter - Minimum	0.23
Conductor Diameter Range	0.23 - 0.57

Logistics

Pallet Quantity	800
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Deadends For Overhead Connections](#)
- [Sales Drawings - GDW420A/GDW440A Single Leg, Wedge Type Deadend \(CC-19265\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-GDW2040A-SPEC-EN | REV 6/2024