


Mid Span Tap

By FARGO
Catalog # [GM125A](#)



*Representative Image

Features

- The Fargo GM125A utilizes the aluminum 4 tap connector block and an aluminum base or body with side loops for attachment of service deadends.
- The use of high strength aluminum washer head bolts permits ease of installation on either open wire or triplex secondary neutrals away from the poles.

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	GM125A
EU RoHS Indicator	No
Material	Aluminum Alloy
Material - Body	Aluminum Alloy
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Product Category	Midspan
Style	Side Hook Connection
Type	Bolted
UPC	096359312390

Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Weight	0.63 lb

Conductor Related

Conductor Diameter - Maximum	0.563
Conductor Diameter - Minimum	0.198
Conductor Diameter Range	0.198 - 0.563

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - CC-26150](#)
- [Specifications - GM125A](#)