

HUBBELL

Power Systems

Automatic Side Opening Wedge Deadend, 4/0 - 600 AAC, 559.5 AAC, 556.5 ACSR, 600 str CU

By FARGO
Catalog # [GDW556A](#)

Automatic Side Opening Wedge Deadend, AAC, AAAC, ACSR, Metric Conductor .520 - .90" (13.2 - 22.8 mm),



*Representative Image

Features

- Fastest method of deadending ACSR, AAAC, and AAC conductor
- Requires no wrenches or special tools
- Rotated clevis eases placement of conductor
- Plated jaws available to accommodate copper conductors

General

Catalog Number	GDW556A
Material	Aluminum Alloy
Material - Body	Aluminum Alloy
Material - Jaw	Aluminum Alloy
Material - Keeper	High Strength Aluminum Alloy
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Product Category	Wedge
Type	Automatic Side Opening Wedge
UPC	096359309888

Dimensions

Assembly Rating (Ultimate)	10000 lb
Dimensions	16.200 in x 5.250 in x 5.670 in
Height	5.67 in
Length	16.2 in
Weight	5.067 lb
Width	5.25 in

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAAC 6201 Alloy-Alliance-246.9-6/18
Conductor Diameter - Maximum	0.9
Conductor Diameter - Minimum	0.52
Conductor Diameter Range	0.52 - 0.9

Logistics

Pallet Quantity	240
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Deadends For Overhead Connections](#)
- [Sales Drawings - GDW420A/GDW440A Single Leg, Wedge Type Deadend \(CC-19265\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-GDW556A-SPEC-EN | REV 6/2024