

HUBBELL

Power Systems

Lightning Arrester Accessory, Aluminum, 4/0 -795 AAC

By FARGO
Catalog # [GH202AD](#)

Overhead Primary Tap, Lightning Arrester, Aluminum, AAC-AAAC-ACSR, Range 0.522 - 1.028 in



*Representative Image

Features

Vise type action develops vibration proof connection on conductor.

General

Bolt Installation Torque (Recommended)	300 in-lbs
Catalog Number	GH202AD
EU RoHS Indicator	No
Hot Stick Eyes	Yes
Inhibitor Loaded	No
Material	Aluminum Alloy
Material - Body	Aluminum Alloy
Material - Eyestem	Aluminum Alloy
Material - Keeper	Aluminum Alloy
Material - Spring (on Eyestem)	Stainless Steel
Number of Hot Stick Eyes	1
Plating	No
Type	Hot Line Specialty Clamp
UPC	096359310419

Dimensions

Diameter - Bolt	0.5 in
Weight	0.559 lb
Width	1.5 in

Conductor Related

Conductor Compatibility

ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Brahma-203.2-16/19;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18

Conductor Diameter - Maximum

1.028 in

Logistics

Packaging Type

Box

Pallet Quantity

2100

Product Assets

[Catalogs - Distribution Connectors](#)

Conductor Diameter - Minimum 0.522 in
Conductor Diameter Range 0.522 - 1.028
Conductor Type Aluminum



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-GH202AD-SPEC-EN | REV 6/2024