


# HUBBELL

## Power Systems

### Compression Terminal 15 degree, Partial Tension

By FARGO  
Catalog # JTF16

Jumper terminals are prefilled with inhibitor. Tongue holes have NEMA spacing. Standard hardware includes one aluminum 1/2 - 13 bolt, nut, and two aluminum washers per .56 diameter hole. Jumper terminals for conductors 1.00 inch diameter or larger are EHV rated.



\*Representative Image

#### Features

- "Jumper terminals are prefilled with inhibitor
- Standard hardware includes Aluminum 1/2-13 bolt, nut and two aluminum washers
- Add "SS" suffix to specify stainless steel hardware
- Die Size: 16CD
- Minimum Press: 60"

#### General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	JTF16
Compression Method	Uni-Grip (single die system)
Die Size	16CD
EU RoHS Indicator	No
Material & Connection Method	Aluminum Compression
Number of Bolt Holes	0
Number of Pad Holes	4
Number of Tees	0
Press Minimum	60 to
Product Category	Compression Jumper Terminal
Tension Range	0 lb
UPC	096359401193

#### Dimensions

Angle - Pad	0 °
Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Outside	0 in
Diameter - Pad Bolt	0 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	14.2 in
Messenger Diameter Range	0 - 0
Nominal Guy Wire Size	0 in
Thickness - Pad	0 in
Weight	3.949 lb
Width - Pad	3 in

#### Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

#### Conductor Related

Conductor Compatibility	ACSR-Bobolink-1431-45/7;ACSR-Plover-1431-54/19;ACSR-Nuthatch-1510.5-45/7;ACSR-Parrot-1510.5-54/19;ACSR-Lapwing-1590-45/7;AAC-Coreopsis-1590-61
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	0 in
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
FG-JTF16-SPEC-EN | REV 6/2024