


## Mid Span Tap Assembly

By FARGO  
Catalog # [GM1091A](#)

Mid Span Tap Assembly



\*Representative Image

### Features

- The Fargo GM1091A is easily installed by swiveling the keepers over the run conductor.
- Double clamping of the run provides parallel current paths.
- Side opening keepers permit easy insertion and quick connections.
- Either tap can be installed or removed without unclamping the run conductor and installation is made without disassembly.

### General

EU RoHS Indicator	No
Material	Aluminum Alloy
Material - Body	Aluminum Alloy
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Product Category	Midspan
Style	Side Loop Connection
Type	Bolted
UPC	096359312369

### Dimensions

Dimensions	3.375 in x 2.063 in x 1.875 in
Height	1.875 in
Length	3.375 in
Weight	0.510 lb
Width	2.063 in

### Conductor Related

Conductor Diameter - Maximum	0.563
Conductor Diameter - Minimum	0.198
Conductor Diameter Range	0.198 - 0.563

### Logistics

Carton Quantity	50
-----------------	----

### Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Literature - Ropes Course Industry Letter \(April 2021\)](#)  
[Sales Drawings - CC-26150](#)

### Related Products

[GM125A - Mid Span Tap](#)  
[GM124A - Mid Span Tap](#)  
[GM104A - Mid Span Tap](#)