


HUBBELL Power Systems

Mid Span Tap

By FARGO
Catalog # [GM124A](#)

Mid Span Tap



*Representative Image

Features

- The Fargo GM124A combination connector and deadend provides both electrical and mechanical neutral connections for secondary service drops.
- Service deadends of either rigid or flexible bail types may be easily installed on the projecting hooks of the body of the clamp.
- The design of the hook retains the bail in position during vibration or shock loading of either the secondary neutral or the service.

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	GM124A
EU RoHS Indicator	No
Material	Aluminum Alloy
Material - Body	Aluminum Alloy
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Product Category	Midspan
Style	Side Loop Connection
Type	Bolted
UPC	096359312376

Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Dimensions	7.000 in x 2.875 in x 2.625 in
Height	2.625 in
Length	7 in
Weight	0.92 lb
Width	2.875 in

Conductor Related

Conductor Diameter - Maximum	0.563
Conductor Diameter - Minimum	0.198
Conductor Diameter Range	0.198 - 0.563

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalogs - Distribution Connectors](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - CC-26150](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-GM124A-SPEC-EN | REV 6/2024