

HUBBELL Power Systems

Compression Terminal 15 degree, Partial Tension

By FARGO
Catalog # JTF08

Jumper terminals are prefilled with inhibitor. Tongue holes have NEMA spacing. Standard hardware includes one aluminum 1/2 - 13 bolt, nut, and two aluminum washers per .56 diameter hole. Jumper terminals for conductors 1.00 inch diameter or larger are EHV rated.

Features

- "Jumper terminals are prefilled with inhibitor
- Standard hardware includes Aluminum 1/2-13 bolt, nut and two aluminum washers
- Add "SS" suffix to specify stainless steel hardware
- Die Size: 08CD
- Minimum Press: 12"

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	JTF08
Compression Method	Uni-Grip (single die system)
Die Size	08CD
EU RoHS Indicator	No
Material & Connection Method	Aluminum Compression
Number of Bolt Holes	0
Number of Pad Holes	2
Number of Tees	0
Press Minimum	12 to
Product Category	Compression Jumper Terminal
Tension Range	0 lb
UPC	096359384083

Dimensions

Angle - Pad	0 °
Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Outside	0 in
Diameter - Pad Bolt	0 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	8.8 in
Messenger Diameter Range	0 - 0
Nominal Guy Wire Size	0 in
Thickness - Pad	0 in
Weight	0.755 lb
Width - Pad	1.7 in



Electrical Ratings

Voltage Application Standard

Conductor Related

Conductor Compatibility	ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Canna-397.5-19
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	0 in
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-JTF08-SPEC-EN | REV 6/2024