

# HUBBELL

## Power Systems

### Compression Terminal 15 degree, Partial Tension

By FARGO  
Catalog # JTF12

Jumper terminals are prefilled with inhibitor. Tongue holes have NEMA spacing. Standard hardware includes one aluminum 1/2 - 13 bolt, nut, and two aluminum washers per .56 diameter hole. Jumper terminals for conductors 1.00 inch diameter or larger are EHV rated.



\*Representative Image

#### Features

- "Jumper terminals are prefilled with inhibitor
- Standard hardware includes Aluminum 1/2-13 bolt, nut and two aluminum washers
- Add "SS" suffix to specify stainless steel hardware
- Die Size: 12CD
- Minimum Press: 60"

#### General

|  |                              |
|--|------------------------------|
| Bolt Installation Torque (Recommended) | 0 ft-lbs                     |
| Catalog Number                         | JTF12                        |
| Compression Method                     | Uni-Grip (single die system) |
| Die Size                               | 12CD                         |
| Material & Connection Method           | Aluminum Compression         |
| Number of Bolt Holes                   | 0                            |
| Number of Pad Holes                    | 4                            |
| Number of Tees                         | 0                            |
| Press Minimum                          | 60 to                        |
| Product Category                       | Compression Jumper Terminal  |
| Tension Range                          | 0 lb                         |
| UPC                                    | 096359384106                 |

#### Dimensions

|                                    |          |
|------------------------------------|----------|
| Angle - Pad                        | 0 °      |
| Assembly Rating (Ultimate)         | 0 lb     |
| Diameter - Bolt                    | 0 in     |
| Diameter - Outside                 | 0 in     |
| Diameter - Pad Bolt                | 0 in     |
| Insulator / Conductor Hole Spacing | 0 in     |
| Length Before Compression          | 11.5 in  |
| Messenger Diameter Range           | 0 - 0    |
| Nominal Guy Wire Size              | 0 in     |
| Thickness - Pad                    | 0 in     |
| Weight                             | 1.882 lb |
| Width - Pad                        | 3 in     |

#### Electrical Ratings

|                     |               |
|---------------------|---------------|
| Voltage Application | EHV; Standard |
|---------------------|---------------|

#### Conductor Related

|                                     |   |
|-------------------------------------|---|
| Conductor Compatibility             | ACSR-Starling-715.5-26/7;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61;AAC-Magnolia-954-37;AAC-Goldenrod-954-61 |
| Conductor Diameter (Main) - Maximum | 0 in  |
| Conductor Diameter (Main) - Minimum | 0 in  |
| Conductor Diameter (Main) Range     | 0 - 0   |
| Conductor Diameter - Maximum        | 0 in  |
| Messenger Diameter - Maximum        | 0 in  |
| Messenger Diameter - Minimum        | 0 in  |

#### Logistics

|                 |     |
|-----------------|-----|
| Pallet Quantity | 300 |
|-----------------|-----|

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
FG-JTF12-SPEC-EN | REV 6/2024