

## Compression Deadend

By FARGO  
Catalog # [SEDA4418SSACNT](#)

Compression Deadend, Conventional 2-Die, Single Tongue, for ACSS 1033.5 kcmil 45/7, Without Terminal



\*Representative Image

### Features

- For use with ACSS code name Ortolan
- Must use High-Temp compound HTJC16
- Full tension Deadend assembly
- Joint Compound purchased separately
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

### General

Aluminum Die	34AH
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	60 to
Product Category	Assemblies
Style	Conventional 2-Die, Single Tongue
Terminal Option	No
Type	Compression

### Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Outside	1.212 in
Length Before Compression	24.1 in
Messenger Diameter Range	0 - 0
Width - Pad	3 in

### Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

### Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSS-Ortolan-1033.5-45/7
Conductor Diameter (Main) Range	0 - 0

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)

[Video - Installation of Hubbell's Conventional Compression Deadends for ACSR and ACSS Conductors\(VI05053E0720\)](#)