

HUBBELL

Power Systems

Formed Wire Double Top Tie, C & F Neck Insulator

By FARGO
Catalog # [LDID0795](#)



C & F Neck Insulator Double Top Tie for 636, 715.5 and 795
ACSR- 795 AAC

Features

- For securing the conductor in the top groove of the insulator on line angles less than 10 degrees with the insulator in a vertical orientation.
- C-Neck (2-1/4" neck diameter) & F-Neck (2-7/8" neck diameter) interchangeable headstyle insulators
- Recommended for use with ANSI Class 55-2 Pin, 55-3 Pin, 55-4 Pin, 55-5 Pin, 57-1 Post, 57-2 Post, & 57-3 Post Insulators.

General

Application	Double Top Tie
Color Code	Green
EU RoHS Indicator	No
Insulator Throat Neck Type	C & F Neck
Material	Aluminum Clad Steel
Product Category	Ties
Type	Formed Wire
UPC	096359452690

Dimensions

Length	22 in
Weight	.600 lb

Conductor Related

Conductor Diameter - Maximum	1.096
Conductor Diameter - Minimum	0.969
Conductor Diameter Range	0.969 - 1.096
Conductor Type	ACSR, AAC, AAAC, Compacted ACSR, Compacted AAC and AWAC®

Logistics

Carton Quantity	50
Pallet Quantity	800

Product Assets

[Sales Drawings - LDID0 Double Top Tie C F-Neck Drawing](#)
[Video - Hubbell Power Systems Double Support Tie Installation](#)



A Hubbell brand