

## Formed Wire Double Side Tie, C & F Neck Insulator

By FARGO  
Catalog # [LLDU4164AS](#)

C & F Neck Insulator Double Side Tie for 796, 954 and 1033.5 ACSR; 954, 1033.5 and 1113 AAC



### Features

- For securing the conductor in the side groove of insulators on line angles between (0°) zero degrees and (80°) eighty degrees with no more than a (40°) forty degree angle at each insulator.
- C-Neck (2-1/4" neck diameter) & F-Neck (2-7/8" neck diameter) interchangeable headstyle insulators
- Recommended for use with ANSI Class 55-2 Pin, 55-3 Pin, 55-4 Pin, 55-5 Pin, 57-1 Post, 57-2 Post, & 57-3 Post Insulators.

### Application

Double Side Tie

### General

Color Code	Yellow
Insulator Throat Neck Type	C & F Neck
Material	Aluminum Clad Steel
Product Category	Ties
Type	Formed Wire
UPC	096359497578

### Dimensions

Length	24.0 in
Weight	.880 lb

### Conductor Related

Conductor Diameter - Maximum	1.24
Conductor Diameter - Minimum	1.097
Conductor Diameter Range	1.097 - 1.24
Conductor Type	ACSR, AAC, AAAC, ACAR, Compacted ACSR and AWAC®

### Logistics

Carton Quantity	50
Pallet Quantity	800

### Product Assets

[Sales Drawings - LLDU4, LLDU5 Drawing](#)

[Video - Hubbell Power Systems Double Side Tie Installation \(VI05009E\)](#)