

Compression Deadend

By FARGO
Catalog # [SEDA5224NT](#)

Compression Deadend, Conventional 2-Die, Single Tongue, for ACSR 1351.5 kcmil 54/19, Without Terminal



*Representative Image

Features

- For use with ACSR code name Martin
- Full tension Deadend assembly
- Joint Compound purchased separately
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

Aluminum Die	38AH
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	60 to
Product Category	Assemblies
Style	Conventional 2-Die, Single Tongue
Terminal Option	No
Type	Compression

Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Outside	1.424 in
Length Before Compression	22.4 in
Messenger Diameter Range	0 - 0
Width - Pad	3 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Martin-1351.5-54/19
Conductor Diameter (Main) Range	0 - 0

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)

[Video - Installation of Hubbell's Conventional Compression Deadends for ACSR and ACSS Conductors\(VI05053E0720\)](#)