

HUBBELL

Power Systems

Compression Deadend

By FARGO

Catalog # [SEDA5718SSACNT](#)

Full-tension deadend assemblies for ACSR conductors consist of an aluminum deadend body, steel deadend eye, 15° jumper terminal and terminal mounting hardware. Terminal and tongue have NEMA hole spacing.



Features

- For use with ACSS code name Lapwing
- Must use High-Temp compount HTJC16
- Full tension Deadend assembly
- Joint Compound purchased separately
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

Aluminum Die	40AH
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	SEDA5718SSACNT
Compression Method	Conventional (2 die system)
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	4
Number of Pad Holes	0
Press Minimum	60 to
Product Category	Assemblies
Style	Conventional 2-Die, Single Tongue
Tension Range	0 lb
Terminal Option	No
Type	Compression
UPC	096359504344

Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Outside	1.504 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	27.3 in
Messenger Diameter Range	0 - 0
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	20.58 lb
Width - Pad	4 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Clamping Range	0 - 0
Conductor Compatibility	ACSS-Lapwing-1590-45/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Video - Installation of Hubbell's Conventional Compression Deadends for ACSR and ACSS Conductors](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-SEDA5718SSACNT-SPEC-EN | REV 6/2024