

## Compression Deadend

By FARGO  
Catalog # [SEDA1309](#)

Full-tension deadend assemblies for ACSR conductors consist of an aluminum deadend body, steel deadend eye, 15° jumper terminal and terminal mounting hardware. Terminal and tongue have NEMA hole spacing.



### Features

- For use with ACSR code name Linnet
- Full tension Deadend assembly
- Joint Compound purchased separately
- Jumper Terminal & Mounting Hardware included

### General

Aluminum Die	20AH
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	SEDA1309
Compression Method	Conventional (2 die system)
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	2
Number of Pad Holes	0
Press Minimum	12 to
Product Category	Assemblies
Style	Conventional 2-Die, Single Tongue
Tension Range	0 lb
Type	Compression
UPC	096359526223

### Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Outside	0.72 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	13.9 in
Messenger Diameter Range	0 - 0
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	1.96 lb
Width - Pad	2 in

### Electrical Ratings

Voltage Application	Standard
---------------------	----------

### Conductor Related

Clamping Range	0 - 0
Conductor Compatibility	ACSR-Linnet-336.4-26/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)  
[Video - Installation of Hubbell's Conventional Compression Deadends for ACSR and ACSS Conductors](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
FG-SEDA1309-SPEC-EN | REV 6/2024