

Compression Deadend

By FARGO
Catalog # [SEDA1309SSAC](#)

Compression Deadend, Conventional 2-Die, Single Tongue, for ACSS 336.4 kcmil 26/7, With Terminal



*Representative Image

Features

- For use with ACSS code name Linnet
- Must use High-Temp compount HTJC16
- Full tension Deadend assembly
- Joint Compound purchased separately
- Jumper Terminal & Mounting Hardware included

General

Aluminum Die	20AH
Compression Method	Conventional (2 die system)
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	2
Press Minimum	12 to
Product Category	Assemblies
Style	Conventional 2-Die, Single Tongue
Type	Compression
UPC	096359504290

Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Outside	0.72 in
Length Before Compression	16.9 in
Messenger Diameter Range	0 - 0
Width - Pad	2 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSS-Linnet-336.4-26/7
Conductor Diameter (Main) Range	0 - 0

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)

[Video - Installation of Hubbell's Conventional Compression Deadends for ACSR and ACSS Conductors\(VI05053E0720\)](#)