

# Compression Splice Conventional (Two Die) Full Tension ACSR Conductor

By FARGO  
Catalog # [TJA3009](#)



\*Representative Image

## Features

- 
- 
- 
- 
- 
- 
- 
- 

## General

Aluminum Die	30AH
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	60 to
Tension Range	0 lb

## Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Diameter - Outside	1.051 in
Insulator / Conductor Hole	0 in
Spacing	
Length Before Compression	27.2 in
Messenger Diameter Range	0 - 0

## Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

## Conductor Related

Conductor Compatibility	ACSR-Starling-715.5-26/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

## Certifications And Compliance

UL Listed	No
-----------	----

## Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
FG-TJA3009-SPEC-EN | REV 6/2024