

Compression Deadend

By FARGO
Catalog # [SEDA2512SSAC](#)

Compression Deadend, Conventional 2-Die, Single Tongue, for ACSS 636.0 kcmil 36/1, With Terminal



*Representative Image

Features

- For use with ACSS code name Aug
- Must use High-Temp compound HTJC16
- Full tension Deadend assembly
- Joint Compound purchased separately
- Jumper Terminal & Mounting Hardware included

General

Aluminum Die	27AH
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	60 to
Product Category	Assemblies
Style	Conventional 2-Die, Single Tongue
Type	Compression

Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Outside	0.93 in
Length Before Compression	19.13 in
Messenger Diameter Range	0 - 0
Width - Pad	3 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	0 - 0
Conductor Diameter (Main) Range	0 - 0

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)

[Video - Installation of Hubbell's Conventional Compression Deadends for ACSR and ACSS Conductors\(VI05053E0720\)](#)