

# HUBBELL

## Power Systems

### Compression Splice Conventional (Two Die) Full Tension ACSR Conductor

By FARGO  
Catalog # [TJA3821](#)

Splice assemblies for ACSR conductors consist of an aluminum splice body and steel sleeve. Material: body - seamless extruded aluminum tube, steel sleeve - plated steel.



\*Representative Image

#### Features

- For use with ACSR code name Canary
- Full tension Splice assembly
- Joint Compound purchased separately

#### General

Aluminum Die	30AH
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	60 to
Tension Range	0 lb
UPC	096359740049

#### Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Diameter - Outside	1.162 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	29.4 in
Messenger Diameter Range	0 - 0

#### Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

#### Conductor Related

Conductor Compatibility	ACSR-Canary-900-54/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

#### Certifications And Compliance

UL Listed  No

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
FG-TJA3821-SPEC-EN | REV 6/2024