

## Compression Deadend

By FARGO  
Catalog # [SEDA6205](#)

Compression Deadend, Conventional 2-Die, Single Tongue, for ACSR 2034.5 kcmil 72/7, With Terminal



\*Representative Image

### Features

- For use with ACSR code name Mockingbird
- Full tension Deadend assembly
- Joint Compound purchased separately
- Jumper Terminal & Mounting Hardware included

### General

Aluminum Die	42AH
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	100 to
Product Category	Assemblies
Style	Conventional 2-Die, Single Tongue
Type	Compression
UPC	096359731726

### Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Outside	1.681 in
Length Before Compression	24.6 in
Messenger Diameter Range	0 - 0
Width - Pad	4 in

### Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

### Conductor Related

Clamping Range	0- 0
Conductor Diameter (Main) Range	0 - 0

### Logistics

Pallet Quantity	30
-----------------	----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)

[Video - Installation of Hubbell's Conventional Compression Deadends for ACSR and ACSS Conductors\(VI05053E0720\)](#)