

HUBBELL Power Systems

Compression Deadend

By FARGO

Catalog # [SEDA6425NT](#)

Full-tension deadend assemblies for ACSR conductors consist of an aluminum deadend body, steel deadend eye, 15° jumper terminal and terminal mounting hardware. Terminal and tongue have NEMA hole spacing.



Features

- For use with ACSR code name Kiwi
- Full tension Deadend assembly
- Joint Compound purchased separately
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

Aluminum Die	44AH
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	SEDA6425NT
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	4
Number of Pad Holes	0
Press Minimum	100 to
Product Category	Assemblies
Style	Conventional 2-Die, Single Tongue
Tension Range	0 lb
Terminal Option	No
Type	Compression

Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Outside	1.735 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	26.1 in
Messenger Diameter Range	0 - 0
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Width - Pad	4 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Clamping Range	0 - 0
Conductor Compatibility	ACSR-Kiwi-2167-72/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Video - Installation of Hubbell's Conventional Compression Deadends for ACSR and ACSS Conductors](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-SEDA6425NT-SPEC-EN | REV 6/2024