

# HUBBELL

## Power Systems

### Compression Splice Conventional (Two Die) Full Tension ACSS Conductor

By FARGO  
Catalog # [TJA6810SSAC](#)

Splice assemblies for ACSS conductors consist of an aluminum splice body and steel sleeve. Material: body - seamless extruded aluminum tube, steel sleeve - plated steel.



\*Representative Image

#### Features

- For use with ACSS code name Joree
- Full tension Splice assembly
- For use with HTJC Joint Compound sold separately

#### General

Aluminum Die	48AH
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	100 to
Tension Range	0 lb

#### Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Diameter - Outside	1.88 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	50 in
Messenger Diameter Range	0 - 0

#### Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

#### Conductor Related

Conductor Compatibility	ACSS-Joree-2515-76/19
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSS
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

#### Certifications And Compliance

UL Listed	No
-----------	----

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
FG-TJA6810SSAC-SPEC-EN | REV 6/2024