

Shield Wire Helical Cushioned Suspension Clamp Assembly

By FARGO
Catalog # [SWHCSAAW0342](#)

"The SWHCSA is a bolted aluminum suspension clamp. It is designed to provide enhanced conductor support and protection. The SWHCSA combines a cast aluminum clamp assembly with helical aluminum alloy rod sets and EPDM rubber inserts. The rubber inserts are assembled directly onto the conductor and are held in place with helical rods. The clamp assembly is then bolted around the helical wrapped rubber supporting inserts to complete the install. Material: Clamp Body & Strap-Aluminum Alloy, Rubber Insert-EPDM Rubber, Helical Rods-Aluminum Alloy, Clamping Range-0.356"-0.374" & Helical Rod Color Code-Orange, 10 Rods Per Set"



*Representative Image

Features

- "The SWHCSAAW clamps are used for Alumoweld® overhead shield wire applications. Maximum Takeoff Angle=30°
- Slip load is 15-20% of respective conductor RBS (Contact Hubbell for more Information)
- Application O.D. = (Helical Rod O.D. X 2) + Conductor O.D
- SWHCSA is supplied with BNK and does not include fittings"

General

Type Shield Wire

Logistics

Pallet Quantity 16

Product Assets

[Literature - Suspension Clamps SWHCSA \(SF05158E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - CC-27007](#)

Related Products

[DSWHCSAAW0342 - Double Shield Wire Helical Cushioned Suspension Clamp Assembly](#)
[SA05 - Socket Eye](#)
[CA05 - Clevis Eye Fitting](#)
[YCS059030 - Y-Clevis Eye, Rotated](#)