

HUBBELL

Power Systems

Compression Splice Conventional (Two Die) Full Tension ACSR Conductor

By FARGO
Catalog # [TJA7929](#)



*Representative Image

Splice assemblies for ACSR conductors consist of an aluminum splice body and steel sleeve. Material: body - seamless extruded aluminum tube, steel sleeve - plated steel.

Features

- For use with ACSR code name Penguin
- Full tension Splice assembly
- Joint Compound purchased separately

General

Aluminum Die	75AH
Compression Method	Conventional (2 die system)
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	12 to
Tension Range	0 lb
UPC	096359482697

Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Diameter - Outside	0.563 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	15.6 in
Messenger Diameter Range	0 - 0
Weight	0.98 lb

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSR-Penguin-4/0-6/1
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	900
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-TJA7929-SPEC-EN | REV 6/2024