


Connector, Vise-Type

by FARGO
Catalog ID: GA9844GL

Single Bolt Aluminum Vise-Type Connector



* Representative image

Product Details

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	300 lb/ft
Cover Available	No
Grommets	Yes
Inhibitor Loaded	Yes
Material	Aluminum Alloy
Material - Body	Aluminum Alloy
Material - Bolt	Aluminum Alloy
Material - Hardware	Aluminum Alloy
Material - Keeper	Aluminum Alloy
Material - Spacer	Aluminum
Plating	No
Product Category	Clamps
Style	Single Bolt
UPC	096359305231

Dimensions

Bolt Diameter	0.500 in
Diameter - Bolt	0.5 in
Diameter - Bolt Head	0.75 in
Height	4.750 in
Length	2.000 in
Length - Nut Flat-To-Flat	0.75 in
Weight	1.215 lb
Width	3.000 in

Conductor Related

Conductor Compatibility	ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Brahma-203.2-16/19;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Tulip-336.1-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Snapdragon-900-61;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18;ACAR-653.1-12/7;ACAR-739.8-18/19
Conductor Diameter (Main) - Maximum	1.031 in
Conductor Diameter (Main) - Minimum	0.793 in
Conductor Diameter (Main) Range	0.793 - 1.031
Conductor Diameter (Tap) - Maximum	0.727 in
Conductor Diameter (Tap) - Minimum	0.563 in
Conductor Diameter - Maximum	1.031 in
Conductor Diameter - Minimum	0.793 in
Conductor Diameter Range	0.793 - 1.031
Conductor Type	Aluminum/Copper

Certifications and Compliance

UL Listed	No
-----------	----

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com