

Compression Splice Conventional  
(Two Die) Full Tension ACSR  
Conductor

By FARGO  
Catalog # [TJA1102](#)



\*Representative Image

Splice assemblies for ACSR conductors consist of an aluminum splice body and steel sleeve. Material: body - seamless extruded aluminum tube, steel sleeve - plated steel.

Features

- For use with ACSR code name Waxwing
- Full tension Splice assembly
- Joint Compound purchased separately

General

Aluminum Die	76AH
Catalog Number	TJA1102
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	12 to
Tension Range	0 lb

Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Diameter - Outside	0.609 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	17.9 in
Messenger Diameter Range	0 - 0

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSR-Waxwing-266.8-18/1
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Certifications And Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - TJA1102](#)