

Compression Splice Conventional
(Two Die) Full Tension ACSS
Conductor

By FARGO

Catalog # [TJA2509SSAC](#)

Splice assemblies for ACSS conductors consist of an aluminum splice body and steel sleeve. Material: body - seamless extruded aluminum tube, steel sleeve - plated steel.

Features

- For use with ACSS code name Grosbeak
- Full tension Splice assembly
- For use with HTJC Joint Compound sold separately

General

Aluminum Die	27AH
Catalog Number	TJA2509SSAC
Compression Method	Conventional (2 die system)
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	60 to
Tension Range	0 lb
UPC	096359374534

Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Diameter - Outside	0.99 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	32.18 in
Messenger Diameter Range	0 - 0
Weight	5.488 lb

Electrical Ratings



*Representative Image

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSS-Grosbeak-636-26/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSS
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
UL Listed	No

Logistics

Pallet Quantity	120
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - TJA2509SSAC](#)