

Compression Splice Conventional
(Two Die) Full Tension ACSS
Conductor

By FARGO
Catalog # [TJA4117SSAC](#)



*Representative Image

Splice assemblies for ACSS conductors consist of an aluminum splice body and steel sleeve. Material: body - seamless extruded aluminum tube, steel sleeve - plated steel.

Features

- For use with ACSS code name Canvasback
- Full tension Splice assembly
- For use with HTJC Joint Compound sold separately

General

| | |
|--------------------|-----------------------------|
| Aluminum Die | 34AH |
| Catalog Number | TJA4117SSAC |
| Compression Method | Conventional (2 die system) |
| Inhibitor Loaded | No |
| Material | Aluminum; Steel |
| Press Minimum | 60 to |
| Tension Range | 0 lb |
| UPC | 096359609209 |

Dimensions

| | |
|------------------------------------|----------|
| Adjustment Step | 0 in |
| Assembly Rating (Ultimate) | 0 lb |
| Diameter - Outside | 1.248 in |
| Insulator / Conductor Hole Spacing | 0 in |
| Length Before Compression | 35 in |
| Messenger Diameter Range | 0 - 0 |

Electrical Ratings

| | |
|---------------------|---------------|
| Voltage Application | EHV; Standard |
|---------------------|---------------|

Conductor Related

| | |
|-------------------------------------|---------------------------|
| Conductor Compatibility | ACSS-Canvasback-954-30/19 |
| Conductor Diameter (Main) - Maximum | 0 in |
| Conductor Diameter (Main) - Minimum | 0 in |
| Conductor Diameter (Main) Range | 0 - 0 |
| Conductor Type | ACSS |
| Messenger Diameter - Maximum | 0 in |
| Messenger Diameter - Minimum | 0 in |

Certifications And Compliance

| | |
|-----------|----|
| UL Listed | No |
|-----------|----|

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - TJA4117SSAC](#)