

Compression Splice Conventional
(Two Die) Full Tension ACSR
Conductor

By FARGO
Catalog # [TJA4121](#)



*Representative Image

Splice assemblies for ACSR conductors consist of an aluminum splice body and steel sleeve. Material: body - seamless extruded aluminum tube, steel sleeve - plated steel.

Features

- For use with ACSR code name Cardinal
- Full tension Splice assembly
- Joint Compound purchased separately

General

Aluminum Die	30AH
Catalog Number	TJA4121
Compression Method	Conventional (2 die system)
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	60 to
Tension Range	0 lb
UPC	096359482659

Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Diameter - Outside	1.196 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	28.6 in
Messenger Diameter Range	0 - 0
Weight	4.577 lb

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACSR-Cardinal-954-54/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
UL Listed	No

Logistics

Pallet Quantity	90
-----------------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - TJA4121](#)