




Aluminum Automatic Dead End, 2/0 AAC, 2/0 AAAC, 2/0 ACSR Conductor, Semi-Flex Bail.

by FARGO
Catalog ID: GD467

Aluminum Automatic Dead End, 2/0 AAC, 2/0 AAAC, 2/0 ACSR Conductor, Diameter range .400 - .470" (10.15 - 11.94 mm), Semi-Flex Bail.

- Automatic Dead Ends for ACSR, AAC, and AAAC Conductor
- galvanized steel stirrup clevis or Z-bail for primary applications and flexible or semi-flex bails for secondary applications
- Add "N" for neoprene covered Flex or Semi-flex bail
- Add "TA" for pulling eye (clevis bail only)



* Representative image

Product Details

General

Bail Option	Semi-Flex Bail
Color Code	Gray
Material	Aluminum
Material - Bail	Stainless Steel
Material - Shell	High Strength Aluminum Alloy
Product Category	Semi-Flex Bail
Type	Automatic
UPC	096359309239

Dimensions

Assembly Rating (Ultimate)	0 lb
Weight	1.080 lb

Conductor Related

Conductor Compatibility	ACSR-Quail-2/0-6/1;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAAC 6201 Alloy-Anaheim-155.4-6/18
Conductor Diameter - Maximum	0.47 in
Conductor Diameter - Minimum	0.4 in
Conductor Diameter Range	0.4 - 0.47

Logistics

Pallet Quantity	840 EA
-----------------	--------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com

