

## Compression Splice Conventional (Two Die) Full Tension

By FARGO  
Catalog # [TJA4724SSAC](#)

Compression Splice, Conventional 2-Die, Full Tension , for  
ACSS 1113.0 kcmil 54/19



\*Representative Image

### Features

- For use with ACSS code name Finch
- Full tension Splice assembly
- For use with HTJC Joint Compound sold separately

### General

Aluminum Die	34AH
Compression Method	Conventional (2 die system)
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	60 to
UPC	096359374312

### Dimensions

Diameter - Outside	1.293 in
Length Before Compression	36.64 in
Messenger Diameter Range	0 - 0
Weight	9.604 lb

### Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

### Conductor Related

Conductor Compatibility	ACSS-Finch-1113-54/19
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSS

### Certifications and Compliance

UL Listed	No
-----------	----

### Logistics

Pallet Quantity	45
-----------------	----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)