

HUBBELL

Power Systems

Compression Splice Conventional (Two Die) Full Tension ACSS Conductor

By FARGO
Catalog # [TJA4918SSAC](#)



*Representative Image

Splice assemblies for ACSS conductors consist of an aluminum splice body and steel sleeve. Material: body - seamless extruded aluminum tube, steel sleeve - plated steel.

Features

- For use with ACSS code name Bunting
- Full tension Splice assembly
- For use with HTJC Joint Compound sold separately

General

Aluminum Die	34AH
Compression Method	Conventional (2 die system)
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	60 to
Tension Range	0 lb
UPC	096359364139

Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Diameter - Outside	1.302 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	36.64 in
Messenger Diameter Range	0 - 0
Weight	9.114 lb

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACSS-Bunting-1192.5-45/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSS
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	45
-----------------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-TJA4918SSAC-SPEC-EN | REV 6/2024