

Compression Splice Conventional (Two Die) Full Tension

By FARGO
Catalog # [TJA5124](#)

Compression Splice, Conventional 2-Die, Full Tension , for
ACSR 1272.0 kcmil 54/19



*Representative Image

Features

- For use with ACSR code name Pheasant
- Full tension Splice assembly
- Joint Compound purchased separately

General

Aluminum Die	36AH
Compression Method	Conventional (2 die system)
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	60 to
UPC	096359365532

Dimensions

Diameter - Outside	1.382 in
Length Before Compression	32.7 in
Messenger Diameter Range	0 - 0
Weight	8.722 lb

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACSR-Pheasant-1272-54/19
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	60
-----------------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)