

HUBBELL

Power Systems

Compression Splice Conventional (Two Die) Full Tension ACSS Conductor

By FARGO
Catalog # [TJA5424SSAC](#)



*Representative Image

Features

-
-
-
-
-
-
-

General

Aluminum Die	38AH
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Press Minimum	60 to
Tension Range	0 lb

Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Diameter - Outside	1.465 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	40.62 in
Messenger Diameter Range	0 - 0

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACSS-Plover-1431-54/19
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSS
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Certifications And Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-TJA5424SSAC-SPEC-EN | REV 6/2024