



## GUY-HOOK, 12,400 lbs. STRENGTH, 5/8in BOLT SIZE with 9/16in LAG HOLE, w/o BACKSIDE CLEATS

by CHANCE Utility  
Catalog ID: GH5N

Cast ductile iron guy-hook attachment for deadending guy and messenger wire. Minimum ultimate tensile strength is 12,400 lbs. and maximum strand size is 7/16in. Includes 11/16in upper hole and 9/16in lower hole for pole attachment. Smooth backside for non-wood pole installation. Manufactured to specification IEEE C135.90. Common industry slang is Ram's Head or Goat Head.

### Product Details

#### General

Coating	Galvanized, ASTM A-153
Material	Ductile Iron, ASTM A-536
UPC	096359494782

#### Dimensions

Distance From Pole	N/A
Weight	1.36 lb

#### Logistics

Carton Quantity	25 EA
Pallet Quantity	1200 EA

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)