



54EB33EC Rotary Limit Switch 72:1 Long Dwell Cam Type 4

By Gleason Reel
Catalog # [54EB33EC](#)



Rotary Limit Switch 72:1 Long Dwell Cam Type 4

Features

- Standard, Long Dwell or Fine Adjustment Cams
- Easy to Wire and Adjust
- Rugged Die-cast Aluminum Housing
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

General

Application	Designed to serve as pilot controls for magnetic reversing starters and contactors which in turn make and break full voltage between line and load.
Catalog Number	54EB33EC
Product Category	Limit Switches
Series	54
UPC	783246013293

Dimensions

Circuits Normally Closed	3
Circuits Normally Open	3
Maximum Shaft Turns To Trip	60
Contacts	
Minimum Shaft Turns To Trip	2
Contacts	
Over Travel Shaft Turns	10
Reset Shaft Turns	1.5

Certifications And Compliance

Nema Rating 4

Product Assets

[Brochures - Series 54 Rotary Limit Switches](#)
[Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)
[Engineering Drawing - Series 54 Rotary Limit Switch DXF](#)
[Engineering Drawing - Series 54 Rotary Limit Switch DWG](#)
[Installation Manuals - Limit Switch-Series 54 "Standard Adjustment" Maintenance Instructions 626382](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
GRD-54EB33EC-SPEC-EN | REV 6/2024