



# 54BB73EB Rotary Limit Switch 36:1 Fine Adjustment Type 4

By Gleason Reel  
Catalog # 54BB73EB



Rotary Limit Switch 36:1 Fine Adjustment Type 4

### Features

- Standard, Long Dwell or Fine Adjustment Cams
- Easy to Wire and Adjust
- Rugged Die-cast Aluminum Housing
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

### Application

Designed to serve as pilot controls for magnetic reversing starters and contactors which in turn make and break full voltage between line and load.

### General

Catalog Number	54BB73EB
Product Category	Limit Switches
Series	54
UPC	783246013415

### Dimensions

Circuits Normally Closed	2
Circuits Normally Open	2
Maximum Shaft Turns To Trip	32
Contacts	
Minimum Shaft Turns To Trip	1
Contacts	
Over Travel Shaft Turns	3.5
Reset Shaft Turns	0.5

### Certifications And Compliance

Nema Rating	4
-------------	---

### Product Assets

- [Brochures - Series 54 Rotary Limit Switches](#)
- [Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)
- [Engineering Drawing - Series 54 Rotary Limit Switch DXF](#)
- [Engineering Drawing - Series 54 Rotary Limit Switch DWG](#)
- [Installation Manuals - Limit Switch-Series 54 "Fine Adjustment"](#)
- [Maintenance Instructions 626383](#)
- [Specifications - 54BB73EB](#)



A Hubbell brand